

# Compatible Printer List

Updated : 2015-01-01

	Discontinued model
	Compatible and tested
	Compatible but not tested

No	Brand	Model	Printer Language	Interface	770	720	S20	S10	570	520	J10/ J20	370	330	220	FINA/ Salus	230	J05	430	170	320	3.0	2.0	Note	Availability	
1	HP	OfficeJet Pro K550	PCL3 GUI	USB	○	○	○	○	○	○	○	○	X	X	X	■	■	○	◆	X	X	X	PCL	Available	
2		OfficeJet 6000	PCL3 GUI	USB	○	○	○	○	○	○	○	○	X	X	X	○	■	○	◆	X	X	X	PCL	Available	
3		OfficeJet 6100	PCL3 GUI	USB	○	○	○	○	○	○	○	○	X	X	X	○	■	○	◆	X	X	X	PCL	Available	
4		OfficeJet Pro 8100	PCL3 GUI	USB	○	○	○	○	○	○	○	○	X	X	X	○	■	○	◆	X	X	X	PCL	Available	
5		OfficeJet 100 Mobile	PCL3 GUI	USB	○	○	○	○	○	○	○	○	X	X	X	○	■	○	◆	X	X	X	PCL	Available	
6		OfficeJet H470 Mobile	PCL3 GUI	USB	○	○	○	○	○	○	○	○	X	X	X	○	■	○	◆	X	X	X	PCL	Discontinued	
1	Samsung	ML-2540	SPL	USB	○	X	X	○	○	○	○	○	X	X	X	◆	◆	◆	◆	X	X	X	SPL2011	Available	
2		ML-2525	SPL	USB	○	○	○	○	○	○	○	○	X	X	X	○	◆	○	◆	X	X	X	SPL2009	Available	
3		ML-2165W/ML-2168W	SPL	USB	○	○	○	○	○	○	○	○	X	X	X	○	◆	○	◆	X	X	X	SPL2009-600	Available	
4		SL-M2620	SPL	USB	○	X	X	○	○	○	○	○	X	X	X	○	◆	○	◆	X	X	X	SPL2009-600	Available	
5		ML-3310D	SPL, PCL5e	USB	○	○	○	○	○	○	○	○	○(PCL)	○(PCL)	X	○	◆	○	◆	X	X	X	SPL2009-600/PCL	Available	
6		ML-2164	SPL	USB	○	○	○	○	○	○	○	○	X	X	X	○	◆	○	◆	X	X	X	SPL2009-600	Available	
7		ML-2855ND	SPL	USB	○	○	○	○	○	○	○	○	X	X	X	○	◆	○	◆	X	X	X	SPL2009	Available	
8		SL-M2620ND	SPL, PCL5e	USB	○	○	○	○	○	○	○	○	X	X	X	○	◆	○	◆	X	X	X	SPL2009-600	Available	
9		ML-2955ND	SPL, PCL5e	USB	○	○	○	○	○	○	○	○	X	X	X	○	◆	○	◆	X	X	X	SPL2009/PCL	Available	
10		ML-2165/ML-2168	SPL	USB	○	○	○	○	○	○	○	○	X	X	X	○	◆	○	◆	X	X	X	SPL2009-600	Available	
11		SL-M2028	SPL	USB	○	○	○	○	○	○	○	○	X	X	X	○	◆	○	◆	X	X	X	SPL2009-600	Available	
12		SL-M2020W	SPL	USB	○	○	○	○	○	○	○	○	X	X	X	○	◆	○	◆	X	X	X	SPL2009-600	Available	
13		SL-M2022	SPL	USB										X	X	X							X	SPL2009-600	Available
14		SL-M2022W	SPL	USB										X	X	X							X	SPL2009-600	Available
15		SL-M2028W	SPL	USB										X	X	X							X	SPL2009-600	Available
16		ML-2162	SPL	USB										X	X	X							X	SPL2009-600	Available
17		SL-M2820ND	SPL, PCL5e	USB										X	X	X							X	SPL2009-600/PCL	Available
18		SL-M2820DW	SPL, PCL5e	USB										X	X	X							X	SPL2009-600/PCL	Available
19		ML-3310ND	SPL, PCL5e	USB										X	X	X							X	SPL2009-600/PCL	Available
1	Lexmark	E260D	PCL5e/PCL6	USB/Parallel	X	○	○	○	X	○	○	○	○	○	○	○	○	○	◆	○	○	X	PCL	Discontinued	
2		E260DN	PCL5e/PCL6	USB/Parallel	X	○	○	○	X	○	○	○	○	○	○	○	○	○	○	◆	○	○	X	PCL	Discontinued
3		MS-310D	PCL5e/PCL6	USB/Parallel	X	○	○	○	X	○	○	○	○	○	○	○	○	○	○	◆	○	○	X	PCL	Discontinued
4		MS-310DN	PCL5e/PCL6	USB/Parallel																			X	PCL	Available
5		MS-312DN	PCL5e/PCL6	USB/Parallel																			X	PCL	Available
6		E360DN	PCL5e/PCL6	USB/Parallel																			X	PCL	Available
1	Brother	HL-2250DN	PCL6	USB		X	X	○	○	○	○	○	○	○	X	○	○	○	◆	X	X	X	PCL	Available	
2		HL-2270DW	PCL6	USB		○	○	○	○	○	○	○	X	X	X	○	X	○	◆	X	X	X	PCL	Available	
3		HL-5340D	PCL6	USB/Parallel		X	X								X							X	X	PCL	Available
4		HL-5350DN	PCL6	USB/Parallel		X	X								X							X	X	PCL	Available

\*\* Host-based printers are not compatible with InBody.

◆ : via PT500 only.

■ : Compatibility depends on firmware version of InBody.

-> InBody330 - 330DM-0208 or higher version.

-> InBody230 - 230DM-0201 or higher version.

-> InBody430 - 430DM-0102 or higher version.

-> InBody520 - TA520DM-0705 or lower version.

-> Salus(For SPL printers) SADM-06-15CK or higher version.

◎ : Samsung ML-1642K needs its printer firmware upgrade before it may work with InBody520/J10/J20.