

InBody - Printer Compatibility

As of 05-31-2013

	Discontinued
	Compatible_Tested
	Compatible_Not Tested

NO	M/F	Model	Type	Language	I/F	720	S20	S10	520	J10/ J20	370	330	220	FINA/ Salus	230	J05	430	170	320	3.0	2.0	Remarks	Availability		
1	HP	Officejet PRO K550	Inkjet	PCL3 GUI	USB	○	○	○	○	○	○	X	X	X	■	■	○	◆	X	X	X	Overseas Only	Available		
1		ML-1865K		SPL	USB	X	X	○	○	○	○	X	X	X	○	○	○	◆	X	X	X	SPL2011	Discontinued		
2		ML-1865WK		SPL, PCL5e	USB	○	○	○	○	○	○	○	○	△	◆	◆	◆	◆	△	△	X	SPL2009	Discontinued		
3		ML-2580NK		SPL, PCL5e/PCL6	USB	○	○	○	○	○	○	○	○	△	○	○	○	◆	△	△	X	SPL2009	Available		
4		ML-2540		SPL	USB	X	X	○	○	○	○	X	X	X	◆	◆	◆	◆	X	X	X	SPL2011	New Model		
5		ML-2165W/ML-2168W		SPL	USB	○	○	○	○	○	○	X	X	X	○	○	○	◆	X	X	X	SPL2009-600	Available		
6		SL-M2620		SPL	USB	X	X	○	○	○	○	X	X	X	○	○	○	◆	X	X	X	SPL2009-600	New Model		
7	Samsung	ML-3310D	Laser	SPL, PCL5e	USB	○	○	○	○	○	○	○(PCL)	○(PCL)	X	○	○	○	◆	X	X	X	SPL2009-600/PCL	New Model		
8		ML-2164		SPL	USB	○	○	○	○	○	○	○	X	X	X	○	○	○	◆	X	X	X	SPL2009-600	Available	
9		SL-M2620ND		SPL, PCL5e	USB	○	○	○	○	○	○	○	X	X	X	○	○	○	◆	X	X	X	SPL2009-600	Available	
10		ML-2162		SPL	USB																		SPL2009-600	Available	
11		ML-2165/ML-2168		SPL	USB																		SPL2009-600	Available	
12		SL-M2820ND		SPL, PCL5e	USB																		SPL2009-600/PCL	Available	
13		SL-M2820DW		SPL, PCL5e	USB																		SPL2009-600/PCL	Available	
14		ML-3310ND		SPL, PCL5e	USB																		SPL2009-600/PCL	Available	
1	Lexmark	E260D	Laser	PCL5e/PCL6	USB/Parallel	○	○	○	○	○	○	○	○	○	○	○	○	○	◆	○	○	X	3.0 (Korean Logo Not	Discontinued	
2		E260DN		PCL5e/PCL6	USB/Parallel	○	○	○	○	○	○	○	○	○	○	○	○	○	○	◆	○	○	X	3.0 (Korean Logo Not	Available
3		E360DN		PCL5e/PCL6	USB/Parallel																			3.0 (Korean Logo Not	Available
1	Brother	HL-2250DN	Laser	PCL6	USB	X	X	○	○	○	○	○	○	X	○	○	○	◆	X	X	X	3.0 (Korean Logo Not	Available		
2		HL-5340D		PCL6	USB/Parallel																		3.0 (Korean Logo Not	Available	
3		HL-5350DN		PCL6	USB/Parallel																			3.0 (Korean Logo Not	Available

** Host based printers do not work.

△ : Printed via PT300

◆ : Printed via PT500